

## Overview

Universal Serial Bus (USB) port technology has emerged in response to the proliferation of external peripheral devices (scanners, digital cameras, removable drives, etc.), that are increasingly being connected to the latest generation of PCs. The USB behaves in a similar fashion to conventional bus ports (i.e., serial, parallel, PS/2), but is faster, and since it does not require any IRQs, more devices can be attached to the system, and the problem of IRQ conflict is eliminated.

The USB-Parallel Printer Cable allows PCs, notebooks, laptops, and handheld computing devices that support the USB specification to print to any parallel printer via the USB with up to 12 Mbps throughput - which is much faster than standard parallel port speeds. The cable provides true plug-n-play and hot plugging capability - in which the cable is automatically detected by Windows.

For further convenience - especially to users of notebooks, laptops, and handhelds - the cable derives its operating power from the Universal Serial Bus itself, so no bulky external power supply needs to be taken along. And because it is a USB Specification compliant device, the cable supports energy-saving suspend and resume operations.

## System Requirements


- Windows 98 or Windows 2000
- USB Host Controller installed on the system.

1

## Features

- Low power consumption; power from USB connection
- Fully automatic high speed bi-directional communication over parallel port
- Allows current Microsoft Windows printer drivers to print seamlessly to USB
- Full Plug & Play compatible
- IEEE-1284 1994 (bidirectional parallel interface) Specification Compliance
- Windows 98, and 2000 driver Support
- No IRQ Required

## Introduction



## Driver Installation:

1. With your computer booted up, plug the cable into the computer's USB port; its presence is automatically detected, and the *New Hardware Wizard* appears; click on *Next* to continue.
2. In the dialog box that comes up choose *Search for the best drivers for your device*; Click on *Next* to continue.
3. In the dialog box that comes up, choose Drive A as your source; insert the distribution diskette in the floppy (A:) drive; Click on *Next* to continue.
4. The dialog that comes up informs you that it has found the driver; Click on *Next* to continue. The driver file is now copied to your hard disk.
5. After the driver file has been copied to the hard disk, a dialog box appears to tell you that the installation has finished. Click on *Finish*. Windows now finishes up the installation.

2

## Uninstalling the Driver:


If you should ever need to uninstall the driver files, simply do the following:

1. Unplug the cable from the PC
2. Insert the ATEN Mini Disc that came with this package into your **CD-ROM Drive**
3. Run the **UNINST.EXE** program found on the distribution diskette
4. Reboot the computer.

## Printer Installation:

If your printer has already been installed:


1. If the cable is plugged into the computer, unplug it
2. Plug the Centronics end of the cable into the printer; then turn the printer On
3. Plug USB end of the cable into the computer
4. Open the *My Computer* folder; open the *Printers* folder
5. Right Click on your Printer icon; select *Properties* from the menu; select the *Details* folder tab
6. Open the *printer port* listbox by clicking on the arrow
7. Select *LPT2: (STET)* from the list.



3

If your printer has not been previously installed:

1. Follow steps 1-4, above.
2. Double Click on the *Add Printer* icon
3. When prompted, select the printer manufacturer and model from the list provided by the *Add Printer Wizard*
4. When prompted for the printer port, select *LPT2:* (*STET*) from the list
5. Follow the *Wizard's* instructions to complete the installation, and print a test page to ensure that there are no problems.



## Specifications

Function		Specification
Connectors	USB	Type A Plug
	Printer	C-36 Male
Cable Length		30 cm
Power Consumption		90mA (max.)
Power Mode		Bus Powered
Operating Temperature		5 ~ 40o C
Storage Temperature		-20 ~ 60o C
Humidity		0 ~ 80% RH, Noncondensing
Housing		Plastic
Weight		110 g
Dimensions (L x W x H)		43 x 53 x 19.5 mm

## Limited Warranty

IN NO EVENT SHALL THE DIRECT VENDOR'S LIABILITY FOR DIRECT, INDIRECT, SPECIAL, INCIDENTAL, OR CONSEQUENTIAL DAMAGES RESULTING FROM THE USE OF THE PRODUCT, DISK, OR ITS DOCUMENTATION EXCEED THE PRICE PAID FOR THE PRODUCT.

The direct vendor makes no warranty or representation, expressed, implied, or statutory with respect to the contents or use of this documentation, and especially disclaims its quality, performance, merchantability, or fitness for any particular purpose.

The direct vendor also reserves the right to revise or update the device or documentation without obligation to notify any individual or entity of such revisions, or update. For further inquiries, please contact your direct vendor.

## Radio & TV Interference

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to Part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation.

USB  
UNIVERSAL SERIAL BUS

USB-  
PARALLEL  
PRINTER  
CABLE



## USER'S MANUAL

### USB-PARALLEL PRINTER CABLE

Read this guide thoroughly and follow the installation and operation procedures carefully to prevent any damage to the unit and/or any of the devices it connects to.

The package contains:

- 1 USB-Parallel Printer Cable
- 1 Distribution Diskette (with Driver Software)
- 1 User Manual

Check to make sure that all the components are there, and nothing was damaged in shipping. If you encounter a problem, contact your dealer.

©Copyright 1999 ATEN® International Co., Ltd.  
Manual Part No. PAPE-1127-200  
Printed in Taiwan 08/1999

All brand names and trademarks are the registered property of their respective owners.